


THE *MAG-DRO* MITRE SLOT BASE HAS BEEN DESIGNED TO HAVE A TIGHT FIT IN A MITER SLOT.

The following illustrations show various miter slot types and if they will allow for a tight fit with the *MAG-DRO* Mitre Slot Base, for accurate readings.



These two types of miter slots will work together with the Mitre Slot Base for a tight fit.

Miter Slots with a small flange thickness as shown will cause a loose fit for the Mitre Slot Base. The Mitre Slot Base will lock into the slot and in order to be removed will need to be slid out the end.

The Mitre Slot base was not designed for this type of miter slot.